

SC913YN24VFAA3 Cut Sheet



CFA solenoid valve, 3-port (3-way), 2-position, N.C., stainless steel body, Viton seal(s), 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=0.084, 0 psi minimum operating pressure, 24 VAC operating voltage, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC913YN24VFAA3>

Technical Specifications

| | |
|----------------------------|----------------------------------|
| Brand | CFA |
| Item | Valve |
| Working Fluid | Air, inert gas, water or coolant |
| Valve Type | Solenoid process |
| Port Quantity | 3-port (3-way) |
| Number Of Positions | 2 |
| Valve Configuration | N.C. |
| Action | Single solenoid spring return |
| Body Material | Stainless steel |
| Seal Material | Viton |
| Inlet Port | 1/8in female NPT |

| | |
|-----------------------------------|----------------------------|
| Outlet Port | 1/8in female NPT |
| Flow Coefficient | 0.084 |
| Maximum Operating Pressure | 102 psi |
| Minimum Operating Pressure | 0 psi |
| Working Fluid Temperature | 230 deg F maximum |
| Operating Voltage | 24 VAC |
| Power Rating | 6.5 VA |
| Electrical Connection | 11mm DIN style wiring plug |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | YSY12 - MH17997 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SC913YN24VFAA3.pdf>
See store item page for other formats.