

SC921YH24VBBA5F Cut Sheet



CFA solenoid valve bank, (2) stations, 2-port (2-way), N.C., 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=0.14, individual metering, brass body, 24 VAC, 6.5 VA, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC921YH24VBBA5F>

Technical Specifications

Brand	CFA
Item	Valve bank
Valve Type	Solenoid process
Working Fluid	Pneumatic, inert gas, water or coolant
Number of Stations	2
Port Quantity	2-port (2-way)
Number Of Positions	2
Valve Configuration	N.C.
Body Material	Brass
Seal Material	Viton

Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Flow Coefficient	0.14
Metering	Individual
Minimum Operating Pressure	0 psi
Maximum Operating Pressure	203 psi
Working Fluid Temperature	230 °F maximum
Operating Voltage	24 VAC
Power Rating	6.5 VA
Electrical Connection	11mm DIN style wiring plug

Agency Approvals

UL Listed File #	None
UL Recognized File #	YSYI2 - MH17997
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SC921YH24VBBA5F.pdf>
See store item page for other formats.