

# SC941YN16VBBA5F Cut Sheet



CFA solenoid valve bank, (4) stations, 2-port (2-way), N.C., 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=0.14, individual metering, brass body, 24 VDC, 4W, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC941YN16VBBA5F>

## Technical Specifications

<b>Brand</b>	CFA
<b>Item</b>	Valve bank
<b>Working Fluid</b>	Air, inert gas, water or coolant
<b>Valve Type</b>	Solenoid process
<b>Number of Stations</b>	4
<b>Port Quantity</b>	2-port (2-way)
<b>Number Of Positions</b>	2
<b>Valve Configuration</b>	N.C.
<b>Body Material</b>	Brass
<b>Inlet Port</b>	1/4in female NPT
<b>Outlet Port</b>	1/4in female NPT

<b>Flow Coefficient</b>	0.14
<b>Metering</b>	Individual
<b>Maximum Operating Pressure</b>	87 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Operating Voltage</b>	24 VDC
<b>Power Rating</b>	4W
<b>Electrical Connection</b>	11mm DIN style wiring plug
<b>Includes</b>	Individual metering

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	YSY12 - MH17997
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SC941YN16VBBA5F.pdf>  
See store item page for other formats.