

# SCA.3.210 Cut Sheet



SapiSelco winged push in panel nylon cable tie, 5.51in length, 0.14in width, 33.08 lb tensile strength, 1.26in maximum bundle diameter, black. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCA.3.210>

---

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Winged push in panel
<b>Material</b>	Nylon
<b>Length</b>	5.51in
<b>Width</b>	0.14in
<b>Tensile Strength</b>	33.08 lb
<b>Maximum Bundle Diameter</b>	1.26in
<b>Color</b>	Black
<b>UV Resistant</b>	No
<b>Temperature Rating</b>	-58 to +140 °F
<b>Installation Temperature</b>	+14 °F
<b>Flammability</b>	UL 94 V-2
<b>Quantity per Pack</b>	100

---

## Agency Approvals

<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>