

# SCE-10086ELJSS6 Cut Sheet



Saginaw Enviroline Junction series enclosure, NEMA 3R/4/4X/12/13, 10 x 8 x 6in (HxWxD), wall mount, 316L stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-10086ELJSS6>

## Technical Specifications

<b>Brand</b>	Saginaw	<b>Integral Mounting Feet</b>	No
<b>Item</b>	Enclosure	<b>Integral Mounting Flange</b>	No
<b>Series</b>	Enviroline Junction	<b>Dual Access</b>	No
<b>Subpanel</b>	Purchase subpanel separately	<b>Knockouts</b>	No
<b>Slope Top</b>	No	<b>Bottom Gland Plate</b>	No
<b>3-Piece Assembly</b>	No	<b>Material</b>	316L stainless steel
<b>Vented</b>	No	<b>Finish</b>	#4 brush
<b>NEMA Rating</b>	3R/4/4X/12/13	<b>Cover Type</b>	Single-door
<b>IP Rating</b>	IP66	<b>Hinge Type</b>	ELJ removable hinge
<b>Nominal Enclosure Dimensions</b>	10 x 8 x 6in (HxWxD)	<b>Number of Hinges Per Door</b>	2
<b>Enclosure Height</b>	10.00in	<b>Latch Type</b>	1/4-turn semi-flush latch
<b>Enclosure Width</b>	8.00in	<b>Number Of Latches</b>	1
<b>Enclosure Depth</b>	6.18in	<b>Padlockable</b>	No
<b>Mounting</b>	Wall	<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>