

SCE-10086ELJWSS6 Cut Sheet



Saginaw Enviroline Junction series enclosure, NEMA 3R/4/4X/12/13, 10 x 8 x 6in (HxWxD), wall mount, 316L stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush latch, polycarbonate window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-10086ELJWSS6>

Technical Specifications

Brand	Saginaw	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Series	Enviroline Junction	Knockouts	No
Subpanel	Purchase subpanel separately	Bottom Gland Plate	No
Slope Top	No	Material	316L stainless steel
3-Piece Assembly	No	Finish	#4 brush
Vented	No	Cover Type	Single-door
NEMA Rating	3R/4/4X/12/13	Hinge Type	ELJ removable hinge
IP Rating	IP66	Number of Hinges Per Door	2
Nominal Enclosure Dimensions	10 x 8 x 6in (HxWxD)	Latch Type	1/4-turn semi-flush latch
Enclosure Height	10.00in	Number Of Latches	1
Enclosure Width	8.00in	Shelf	No
Enclosure Depth	6.18in	Window Material	Polycarbonate
Mounting	Wall	Padlockable	No
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-10086ELJWSS6.pdf>
See store item page for other formats.