

SCE-12108CHNFSS Cut Sheet



Saginaw enclosure, NEMA 3R/4/4X/12/13, 12 x 10 x 8in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-12108CHNFSS>

Technical Specifications

Brand	Saginaw	Integral Mounting Flange	Yes
Item	Enclosure	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	#4 brush
NEMA Rating	3R/4/4X/12/13	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Continuous hinge
Nominal Enclosure Dimensions	12 x 10 x 8in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	12.38in	Latch Type	Stainless steel clamps
Enclosure Width	10.39in	Number Of Latches	2
Enclosure Depth	8.20in	Shelf	No
Mounting	Wall	Padlockable	No
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-12108CHNFSS.pdf>
See store item page for other formats.