

SCE-14128ELJSS Cut Sheet



Saginaw Enviroline Junction series enclosure, NEMA 3R/4/4X/12/13, 14 x 12 x 8in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-14128ELJSS>

Technical Specifications

Brand	Saginaw	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	No
Series	Enviroline Junction	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	#4 brush
NEMA Rating	3R/4/4X/12/13	Cover Type	Single-door
IP Rating	IP66	Hinge Type	ELJ removable hinge
Nominal Enclosure Dimensions	14 x 12 x 8in (HxWxD)	Number of Hinges Per Door	3
Enclosure Height	14.00in	Latch Type	1/4-turn semi-flush latch
Enclosure Width	12.00in	Number Of Latches	1
Enclosure Depth	8.18in	Padlockable	No
Mounting	Wall	Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement