

SCE-1448BD Cut Sheet



Saginaw operator console, NEMA 3R/12/13, 50 x 48 x 23in (HxWxD), freestanding, dual access, carbon steel, ANSI 61 gray, powder coat finish, double-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-1448BD>

Technical Specifications

Brand	Saginaw
Item	Operator console
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/12/13
IP Rating	IP55
Nominal Enclosure Dimensions	50 x 48 x 23in (HxWxD)
Enclosure Height	50.00in
Enclosure Width	48.00in
Enclosure Depth	25.06in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	Yes
Knockouts	No

Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Double-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Number of Lid Hinges	2
Latch Type	3-point keylocking/padlocking combo handle
Number of Door Latches	1
Secondary Latch Type	1/4-turn semi-flush latch
Number Of Secondary Latches	3
Shelf	No
Padlockable	Yes
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-1448BD.pdf>
See store item page for other formats.