

SCE-14HMI1806LP Cut Sheet



Saginaw HMI Enclosure, NEMA 3R/4/12/13, 14 x 18 x 6in (HxWxD), suspension or pedestal mount, dual access, carbon steel, RAL 7035 light gray, powder coat finish, screw cover front, single door rear, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-14HMI1806LP>

Technical Specifications

Brand	Saginaw
Item	HMI Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	14 x 18 x 6in (HxWxD)
Enclosure Height	14.27in
Enclosure Width	18.27in
Enclosure Depth	7.25in
Mounting	Suspension or pedestal

Dual Access	Yes
Knockouts	No
Material	Carbon steel
Color	RAL 7035 light gray
Finish	Powder coat
Cover Type	Screw cover front, single door rear
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush latch
Number Of Latches	1
Padlockable	No
Keylocking	No
Additional Information	Max front cut-out area 11.5 x 15.5in

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-14HMI1806LP.pdf>
See store item page for other formats.