

# SCE-14HMI1806SSLP Cut Sheet



Saginaw HMI Enclosure, NEMA 3R/4/4X/12/13, 14 x 18 x 6in (HxWxD), suspension or pedestal mount, dual access, 304 stainless steel, #4 brush finish, screw cover front, single door rear, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-14HMI1806SSLP>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	HMI Enclosure
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>3-Piece Assembly</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	3R/4/4X/12/13
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	14 x 18 x 6in (HxWxD)
<b>Enclosure Height</b>	14.27in
<b>Enclosure Width</b>	18.27in
<b>Enclosure Depth</b>	7.25in
<b>Mounting</b>	Suspension or pedestal

<b>Dual Access</b>	Yes
<b>Knockouts</b>	No
<b>Material</b>	304 stainless steel
<b>Finish</b>	#4 brush
<b>Cover Type</b>	Screw cover front, single door rear
<b>Hinge Type</b>	Concealed hinges
<b>Number of Hinges Per Door</b>	2
<b>Latch Type</b>	1/4-turn semi-flush latch
<b>Number Of Latches</b>	1
<b>Padlockable</b>	No
<b>Keylocking</b>	No
<b>Additional Information</b>	Max front cut-out area 11.5 x 15.5in

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-14HMI1806SSLP.pdf>  
See store item page for other formats.