

SCE-16H1208LP Cut Sheet



Saginaw enclosure, NEMA 3R/4/12/13, 16 x 12 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, plated steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-16H1208LP>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Saginaw |
| Item | Enclosure |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 3R/4/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 16 x 12 x 8in (HxWxD) |
| Enclosure Height | 16.00in |
| Enclosure Width | 12.00in |
| Enclosure Depth | 9.07in |
| Mounting | Wall |
| Integral Mounting Feet | Yes |
| Integral Mounting Flange | No |

| | |
|----------------------------------|-------------------------|
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 2 |
| Latch Type | Plated steel clamps |
| Number Of Latches | 2 |
| Padlock Attachment Type | Padlock hasp and staple |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |