

SCE-16PBHSS6 Cut Sheet



Saginaw pushbutton enclosure, 16 holes, 30mm, NEMA 4/4X/12/13, 12 x 12 x 6in (HxWxD), wall mount, 316L stainless steel, #4 brush finish, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-16PBHSS6>

Technical Specifications

Brand	Saginaw
Item	Pushbutton enclosure
Number of Pushbutton Holes	16 holes
Pushbutton Hole Nominal Size	30mm
NEMA Rating	4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	12 x 12 x 6in (HxWxD)
Enclosure Height	12.38in
Enclosure Width	12.31in
Enclosure Depth	6.20in

Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	316L stainless steel
Finish	#4 brush
Cover Type	Hinged screw cover
Hinge Type	Continuous hinge
Number of Hinges Per Door	1

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement