

SCE-16PBHSSI Cut Sheet



Saginaw pushbutton enclosure, 16 holes, 22mm, NEMA 4/4X/12/13, 12 x 12 x 6in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-16PBHSSI>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Saginaw |
| Item | Pushbutton enclosure |
| Number of Pushbutton Holes | 16 holes |
| Pushbutton Hole Nominal Size | 22mm |
| NEMA Rating | 4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 12 x 12 x 6in (HxWxD) |
| Enclosure Height | 12.38in |
| Enclosure Width | 12.31in |
| Enclosure Depth | 6.20in |

| | |
|----------------------------------|---------------------|
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | 304 stainless steel |
| Finish | #4 brush |
| Cover Type | Hinged screw cover |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |