

SCE-1PBSS Cut Sheet



Saginaw pushbutton enclosure, 1 hole, 30mm, NEMA 4/4X/12/13, 4 x 4 x 3in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-1PBSS>

Technical Specifications

Brand	Saginaw
Item	Pushbutton enclosure
Number of Pushbutton Holes	1 hole
Pushbutton Hole Nominal Size	30mm
NEMA Rating	4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	4 x 4 x 3in (HxWxD)
Enclosure Height	3.81in
Enclosure Width	3.56in
Enclosure Depth	2.91in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Screw cover

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement