

SCE-20208ELJW Cut Sheet



Saginaw Enviroline Junction series enclosure, NEMA 3R/4/12/13, 20 x 20 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn semi-flush latch, polycarbonate window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-20208ELJW>

Technical Specifications

Brand	Saginaw
Item	Enclosure
Series	Enviroline Junction
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	20 x 20 x 8in (HxWxD)
Enclosure Height	20.00in
Enclosure Width	20.00in
Enclosure Depth	8.18in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	ELJ removable hinge
Number of Hinges Per Door	3
Latch Type	1/4-turn semi-flush latch
Number Of Latches	2
Window Material	Polycarbonate
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement