

# SCE-20C24ELJSS Cut Sheet



Saginaw operator console, NEMA 3R/4/4X/12/13, 20 x 24 x 13in (HxWxD), desktop or pedestal mount, 304 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-20C24ELJSS>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Saginaw                      |
| <b>Item</b>                         | Operator console             |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>NEMA Rating</b>                  | 3R/4/4X/12/13                |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 20 x 24 x 13in (HxWxD)       |
| <b>Enclosure Height</b>             | 17.84in                      |
| <b>Enclosure Width</b>              | 20.00in                      |
| <b>Enclosure Depth</b>              | 13.09in                      |
| <b>Mounting</b>                     | Desktop or pedestal          |
| <b>Integral Mounting Feet</b>       | No                           |
| <b>Integral Mounting Flange</b>     | No                           |

|                                  |                                     |
|----------------------------------|-------------------------------------|
| <b>Dual Access</b>               | No                                  |
| <b>Knockouts</b>                 | No                                  |
| <b>Material</b>                  | 304 stainless steel                 |
| <b>Finish</b>                    | #4 brush                            |
| <b>Cover Type</b>                | Single-door                         |
| <b>Hinge Type</b>                | ELJ removable hinge                 |
| <b>Number of Hinges Per Door</b> | 2                                   |
| <b>Number of Lid Hinges</b>      | 2                                   |
| <b>Latch Type</b>                | 1/4-turn semi-flush latch           |
| <b>Number Of Latches</b>         | 2                                   |
| <b>Padlockable</b>               | No                                  |
| <b>Keylocking</b>                | No                                  |
| <b>Additional Information</b>    | Purchase pedestal column separately |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |