

SCE-20H1610LP Cut Sheet



Saginaw enclosure, NEMA 3R/4/12/13, 20 x 16 x 10in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, plated steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-20H1610LP>

Technical Specifications

Brand	Saginaw	Dual Access	No
Item	Enclosure	Knockouts	No
Subpanel	Purchase subpanel separately	Bottom Gland Plate	No
Slope Top	No	Material	Carbon steel
3-Piece Assembly	No	Color	ANSI 61 gray
Vented	No	Finish	Powder coat
NEMA Rating	3R/4/12/13	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Concealed hinges
Nominal Enclosure Dimensions	20 x 16 x 10in (HxWxD)	Number of Hinges Per Door	2
Enclosure Height	20.00in	Latch Type	Plated steel clamps
Enclosure Width	16.00in	Number Of Latches	2
Enclosure Depth	11.07in	Padlock Attachment Type	Padlock hasp and staple
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	Yes	Keylocking	No
Integral Mounting Flange	No		

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement