

SCE-20XEL2108LP Cut Sheet



Saginaw Enviroline series disconnect enclosure, NEMA 3R/4/12/13, right flange, 20 x 21 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-20XEL2108LP>

Technical Specifications

Brand	Saginaw	Material	Carbon steel
Item	Disconnect enclosure	Color	ANSI 61 gray
Series	Enviroline	Finish	Powder coat
Slope Top	No	Cover Type	Single-door
Vented	No	Hinge Type	Concealed hinges
NEMA Rating	3R/4/12/13	Number of Hinges Per Door	2
IP Rating	IP66	Latch Type	2-point padlocking handle
Disconnect Mounting	Right flange	Padlockable	Yes
Nominal Enclosure Dimensions	20 x 21 x 8in (HxWxD)	Keylocking	No
Enclosure Height	20.00in	Subpanel	Purchase subpanel separately
Enclosure Width	21.38in	For Use With	Most major brand disconnect switches and circuit breakers
Enclosure Depth	9.10in	Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier
Mounting	Wall		
Integral Mounting Feet	No		
Integral Mounting Flange	No		
Knockouts	No		

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement