

# SCE-244808WFLP Cut Sheet



Saginaw enclosure, NEMA 3R/12/13, 24 x 48 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, double-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-244808WFLP>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Saginaw                      |
| <b>Item</b>                         | Enclosure                    |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | No                           |
| <b>NEMA Rating</b>                  | 3R/12/13                     |
| <b>IP Rating</b>                    | IP55                         |
| <b>Nominal Enclosure Dimensions</b> | 24 x 48 x 8in (HxWxD)        |
| <b>Enclosure Height</b>             | 24.00in                      |
| <b>Enclosure Width</b>              | 48.00in                      |
| <b>Enclosure Depth</b>              | 9.10in                       |
| <b>Mounting</b>                     | Wall                         |
| <b>Integral Mounting Feet</b>       | No                           |

|                                  |  |
|----------------------------------|--|
| <b>Integral Mounting Flange</b>  | No   |
| <b>Dual Access</b>               | No   |
| <b>Knockouts</b>                 | No   |
| <b>Bottom Gland Plate</b>        | No   |
| <b>Material</b>                  | Carbon steel                               |
| <b>Color</b>                     | ANSI 61 gray                               |
| <b>Finish</b>                    | Powder coat                                |
| <b>Cover Type</b>                | Double-door                                |
| <b>Hinge Type</b>                | Concealed hinges                           |
| <b>Number of Hinges Per Door</b> | 2  |
| <b>Latch Type</b>                | 3-point keylocking/padlocking combo handle |
| <b>Number Of Latches</b>         | 1  |
| <b>Padlockable</b>               | Yes  |
| <b>Keylocking</b>                | Yes  |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |