

SCE-24EL4210WFLP Cut Sheet



Saginaw Enviroline series enclosure, NEMA 3R/4/12/13, 24 x 42 x 10in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-24EL4210WFLP>

Technical Specifications

| | | | |
|-------------------------------------|------------------------------|----------------------------------|--|
| Brand | Saginaw | Integral Mounting Flange | No |
| Item | Enclosure | Dual Access | No |
| Series | Enviroline | Knockouts | No |
| Subpanel | Purchase subpanel separately | Bottom Gland Plate | No |
| Slope Top | No | Material | Carbon steel |
| 3-Piece Assembly | No | Color | ANSI 61 gray |
| Vented | No | Finish | Powder coat |
| NEMA Rating | 3R/4/12/13 | Cover Type | 2-door |
| IP Rating | IP66 | Hinge Type | Concealed hinges |
| Nominal Enclosure Dimensions | 24 x 42 x 10in (HxWxD) | Number of Hinges Per Door | 2 |
| Enclosure Height | 24.00in | Latch Type | 3-point keylocking/padlocking combo handle |
| Enclosure Width | 42.00in | Number Of Latches | 2 |
| Enclosure Depth | 11.10in | Shelf | No |
| Mounting | Wall | Padlockable | Yes |
| Integral Mounting Feet | No | Keylocking | Yes |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-24EL4210WFLP.pdf>
See store item page for other formats.