

SCE-24HS2508SSLP Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 24 x 25 x 8in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, stainless steel clamps, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-24HS2508SSLP>

Technical Specifications

Brand	Saginaw
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Height	24in
Nominal Enclosure Width	25.38in
Nominal Enclosure Depth	9.07in
Mounting	Wall
Integral Mounting Feet	No

Material	304 stainless steel
Finish	#4 brush
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	Stainless steel clamps
Padlockable	No
Keylocking	No
Subpanel	Purchase subpanel separately
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-24HS2508SSLP.pdf>
See store item page for other formats.