

SCE-24N2006NK-T Cut Sheet



Saginaw enclosure, NEMA 1, 24 x 20 x 6in (HxWxD), wall mount, with knockouts, carbon steel, taupe tan, powder coat finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-24N2006NK-T>

Technical Specifications

| | |
|-------------------------------------|---------------------------------|
| Brand | Saginaw |
| Item | Enclosure |
| Subpanel | Powder coated subpanel included |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 1 |
| IP Rating | IP30 |
| Nominal Enclosure Dimensions | 24 x 20 x 6in (HxWxD) |
| Enclosure Height | 24.38in |
| Enclosure Width | 20.38in |
| Enclosure Depth | 6.13in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |

| | |
|----------------------------------|---------------------------|
| Dual Access | No |
| Knockouts | Yes |
| Bottom Gland Plate | No |
| Material | Carbon steel |
| Color | Taupe tan |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | Butt hinges |
| Number of Hinges Per Door | 3 |
| Latch Type | 1/4-turn semi-flush latch |
| Number Of Latches | 1 |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-24N2006NK-T.pdf>
See store item page for other formats.