

SCE-24SBASESS Cut Sheet

Saginaw pedestal base, 304 stainless steel, 24.00 x 24.00in, #4 brush finish. For use with console pedestal columns.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-24SBASESS>

Technical Specifications

| | |
|--------------|--------------------------|
| Brand | Saginaw |
| Item | Pedestal base |
| Material | 304 stainless steel |
| Size | 24.00 x 24.00in |
| Finish | #4 brush |
| NEMA Rating | 4/4X/12/13 |
| For Use With | Console pedestal columns |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-24SBASESS.pdf>
See store item page for other formats.