

# SCE-24XEL2508SSLP Cut Sheet



Saginaw Enviroline series disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 24 x 25 x 8in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-24XEL2508SSLP>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Disconnect enclosure
<b>Series</b>	Enviroline
<b>Slope Top</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	3R/4/4X/12/13
<b>IP Rating</b>	IP66
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Dimensions</b>	24 x 25 x 8in (HxWxD)
<b>Enclosure Height</b>	24.00in
<b>Enclosure Width</b>	25.38in
<b>Enclosure Depth</b>	9.10in
<b>Mounting</b>	Wall
<b>Integral Mounting Feet</b>	No
<b>Integral Mounting Flange</b>	No

<b>Knockouts</b>	No
<b>Material</b>	304 stainless steel
<b>Finish</b>	#4 brush
<b>Cover Type</b>	Single-door
<b>Hinge Type</b>	Concealed hinges
<b>Number of Hinges Per Door</b>	2
<b>Latch Type</b>	2-point padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Subpanel</b>	Purchase subpanel separately
<b>For Use With</b>	Most major brand disconnect switches and circuit breakers
<b>Additional Information</b>	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>