

SCE-24XEL2510SSLP Cut Sheet



Saginaw Enviroline series disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 24 x 25 x 10in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-24XEL2510SSLP>

Technical Specifications

Brand	Saginaw	Knockouts	No
Item	Disconnect enclosure	Material	304 stainless steel
Series	Enviroline	Finish	#4 brush
Slope Top	No	Cover Type	Single-door
Vented	No	Hinge Type	Concealed hinges
NEMA Rating	3R/4/4X/12/13	Number of Hinges Per Door	2
IP Rating	IP66	Latch Type	2-point padlocking handle
Disconnect Mounting	Right flange	Padlockable	Yes
Nominal Enclosure Dimensions	24 x 25 x 10in (HxWxD)	Keylocking	No
Enclosure Height	24.00in	Subpanel	Purchase subpanel separately
Enclosure Width	25.38in	For Use With	Most major brand disconnect switches and circuit breakers
Enclosure Depth	11.10in	Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier
Mounting	Wall		
Integral Mounting Feet	No		
Integral Mounting Flange	No		

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement