

SCE-29VR2412 Cut Sheet



Saginaw enclosure, vented, NEMA 3R, 29 x 24 x 12in (HxWxD), wall mount, carbon steel, white, powder coat finish, single-door, 1/4-turn padlocking wing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-29VR2412>

Technical Specifications

Brand	Saginaw
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	Yes
NEMA Rating	3R
IP Rating	IP32
Nominal Enclosure Dimensions	29 x 24 x 12in (HxWxD)
Enclosure Height	29.00in
Enclosure Width	24.00in
Enclosure Depth	13.07in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	White
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn padlocking wing handle
Number Of Latches	1
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement