

SCE-30XEL2510SSST Cut Sheet



Saginaw Enviroline series disconnect enclosure, slope top, NEMA 3R/4/4X/12/13, right flange, 30 x 25 x 10in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-30XEL2510SSST>

Technical Specifications

| | |
|-------------------------------------|------------------------|
| Brand | Saginaw |
| Item | Disconnect enclosure |
| Series | Enviroline |
| Slope Top | Yes |
| Vented | No |
| NEMA Rating | 3R/4/4X/12/13 |
| IP Rating | IP66 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 30 x 25 x 10in (HxWxD) |
| Enclosure Height | 32.65in |
| Enclosure Width | 25.38in |
| Enclosure Depth | 11.10in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |

| | |
|----------------------------------|---|
| Knockouts | No |
| Material | 304 stainless steel |
| Finish | #4 brush |
| Cover Type | Single-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 2 |
| Latch Type | 2-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | Purchase subpanel separately |
| For Use With | Most major brand disconnect switches and circuit breakers |
| Additional Information | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-30XEL2510SSST.pdf>
See store item page for other formats.