

# SCE-342424WS Cut Sheet



Saginaw workstation, NEMA 12/13, 34 x 24 x 24in (HxWxD), desktop or pedestal mount, dual access, carbon steel, RAL 7035 light gray, powder coat finish, single-door with keyboard drawer, 3-point keylocking flush swing handle, polycarbonate window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-342424WS>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Workstation
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>3-Piece Assembly</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	12/13
<b>IP Rating</b>	IP55
<b>Nominal Enclosure Dimensions</b>	34 x 24 x 24in (HxWxD)
<b>Enclosure Height</b>	34.00in
<b>Enclosure Width</b>	24.25in
<b>Enclosure Depth</b>	26.39in
<b>Mounting</b>	Desktop or pedestal
<b>Integral Mounting Feet</b>	No
<b>Integral Mounting Flange</b>	No
<b>Dual Access</b>	Yes
<b>Knockouts</b>	No

<b>Bottom Gland Plate</b>	No
<b>Material</b>	Carbon steel
<b>Color</b>	RAL 7035 light gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Single-door with keyboard drawer
<b>Hinge Type</b>	Concealed hinges
<b>Number of Lid Hinges</b>	2
<b>Latch Type</b>	3-point keylocking flush swing handle
<b>Number of Door Latches</b>	1
<b>Secondary Latch Type</b>	1/4-turn semi-flush latch
<b>Number Of Secondary Latches</b>	2
<b>Shelf</b>	No
<b>Window Material</b>	Polycarbonate
<b>Padlockable</b>	No
<b>Keylocking</b>	Yes
<b>Additional Information</b>	Purchase pedestal column separately

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-342424WS.pdf>  
See store item page for other formats.