

# SCE-36EL4812WFLP Cut Sheet



Saginaw Enviroline series enclosure, NEMA 3R/4/12/13, 36 x 48 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-36EL4812WFLP>

## Technical Specifications

<b>Brand</b>	Saginaw	<b>Integral Mounting Flange</b>	No
<b>Item</b>	Enclosure	<b>Dual Access</b>	No
<b>Series</b>	Enviroline	<b>Knockouts</b>	No
<b>Subpanel</b>	Purchase subpanel separately	<b>Bottom Gland Plate</b>	No
<b>Slope Top</b>	No	<b>Material</b>	Carbon steel
<b>3-Piece Assembly</b>	No	<b>Color</b>	ANSI 61 gray
<b>Vented</b>	No	<b>Finish</b>	Powder coat
<b>NEMA Rating</b>	3R/4/12/13	<b>Cover Type</b>	2-door
<b>IP Rating</b>	IP66	<b>Hinge Type</b>	Concealed hinges
<b>Nominal Enclosure Dimensions</b>	36 x 48 x 12in (HxWxD)	<b>Number of Hinges Per Door</b>	2
<b>Enclosure Height</b>	36.00in	<b>Latch Type</b>	3-point keylocking/padlocking combo handle
<b>Enclosure Width</b>	48.00in	<b>Number Of Latches</b>	2
<b>Enclosure Depth</b>	13.10in	<b>Shelf</b>	No
<b>Mounting</b>	Wall	<b>Padlockable</b>	Yes
<b>Integral Mounting Feet</b>	No	<b>Keylocking</b>	Yes

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-36EL4812WFLP.pdf>  
See store item page for other formats.