

SCE-36N2406NK-T Cut Sheet



Saginaw enclosure, NEMA 1, 36 x 24 x 6in (HxWxD), wall mount, with knockouts, carbon steel, taupe tan, powder coat finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-36N2406NK-T>

Technical Specifications

Brand	Saginaw
Item	Enclosure
Subpanel	Powder coated subpanel included
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1
IP Rating	IP30
Nominal Enclosure Dimensions	36 x 24 x 6in (HxWxD)
Enclosure Height	36.38in
Enclosure Width	24.38in
Enclosure Depth	6.13in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	Yes
Bottom Gland Plate	No
Material	Carbon steel
Color	Taupe tan
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Butt hinges
Number of Hinges Per Door	4
Latch Type	1/4-turn semi-flush latch
Number Of Latches	1
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement