

SCE-36XEL2510LP Cut Sheet



Saginaw Enviroline series disconnect enclosure, NEMA 3R/4/12/13, right flange, 36 x 25 x 10in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-36XEL2510LP>

Technical Specifications

Brand	Saginaw
Item	Disconnect enclosure
Series	Enviroline
Slope Top	No
Vented	No
NEMA Rating	3R/4/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	36 x 25 x 10in (HxWxD)
Enclosure Height	36.00in
Enclosure Width	25.38in
Enclosure Depth	11.10in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Knockouts	No

Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	2-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately
For Use With	Most major brand disconnect switches and circuit breakers
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-36XEL2510LP.pdf>
See store item page for other formats.