

# SCE-36XEL3110LP Cut Sheet



Saginaw Enviroline series disconnect enclosure, NEMA 3R/4/12/13, right flange, 36 x 31 x 10in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-36XEL3110LP>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Disconnect enclosure
<b>Series</b>	Enviroline
<b>Slope Top</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	3R/4/12/13
<b>IP Rating</b>	IP66
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Height</b>	36in
<b>Nominal Enclosure Width</b>	31in
<b>Nominal Enclosure Depth</b>	10in
<b>Mounting</b>	Wall

<b>Integral Mounting Feet</b>	No
<b>Material</b>	Carbon steel
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Single-door
<b>Hinge Type</b>	Concealed hinges
<b>Number of Hinges Per Door</b>	2
<b>Latch Type</b>	2-point padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Subpanel</b>	Purchase subpanel separately

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-36XEL3110LP.pdf>  
See store item page for other formats.