

SCE-402516SDCSS Cut Sheet



Saginaw desk console, NEMA 3R/4/4X/12/13, 40 x 25 x 16in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, single-door, 3-point keylocking flush swing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-402516SDCSS>

Technical Specifications

Brand	Saginaw	Knockouts	No
Item	Desk console	Bottom Gland Plate	No
Subpanel	Purchase subpanel separately	Material	304 stainless steel
Slope Top	No	Finish	#4 brush
3-Piece Assembly	No	Cover Type	Single-door
Vented	No	Hinge Type	Concealed hinges
NEMA Rating	3R/4/4X/12/13	Number of Hinges Per Door	2
IP Rating	IP66	Number of Lid Hinges	2
Nominal Enclosure Dimensions	40 x 25 x 16in (HxWxD)	Latch Type	3-point keylocking flush swing handle
Enclosure Height	41.18in	Number of Door Latches	1
Enclosure Width	25.25in	Secondary Latch Type	1/4-turn semi-flush latch
Enclosure Depth	21.50in	Number Of Secondary Latches	2
Mounting	Freestanding	Shelf	No
Integral Mounting Feet	No	Padlockable	No
Integral Mounting Flange	No	Keylocking	Yes
Dual Access	No		

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-402516SDCSS.pdf>
See store item page for other formats.