

SCE-402516SDC Cut Sheet



Saginaw desk console, NEMA 3R/4/12/13, 40 x 25 x 16in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking flush swing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-402516SDC>

Technical Specifications

Brand	Saginaw
Item	Desk console
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/4/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	40 x 25 x 16in (HxWxD)
Enclosure Height	41.18in
Enclosure Width	25.25in
Enclosure Depth	21.50in
Mounting	Freestanding
Dual Access	No
Knockouts	No
Material	Carbon steel

Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Number of Lid Hinges	2
Latch Type	3-point keylocking flush swing handle
Number of Door Latches	1
Secondary Latch Type	1/4-turn semi-flush latch
Number Of Secondary Latches	2
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement