

SCE-403716SDCSS Cut Sheet



Saginaw desk console, NEMA 3R/12/13/4/4X, 40 x 37 x 16in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, single-door, 3-point keylocking flush swing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-403716SDCSS>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Saginaw |
| Item | Desk console |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 3R/12/13/4/4X |
| IP Rating | IP55 |
| Nominal Enclosure Dimensions | 40 x 37 x 16in (HxWxD) |
| Enclosure Height | 41.18in |
| Enclosure Width | 37.25in |
| Enclosure Depth | 21.50in |
| Mounting | Freestanding |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Dual Access | No |

| | |
|------------------------------------|---------------------------------------|
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | 304 stainless steel |
| Finish | #4 brush |
| Cover Type | Single-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 2 |
| Number of Lid Hinges | 2 |
| Latch Type | 3-point keylocking flush swing handle |
| Number of Door Latches | 1 |
| Secondary Latch Type | 1/4-turn semi-flush latch |
| Number Of Secondary Latches | 2 |
| Shelf | No |
| Padlockable | No |
| Keylocking | Yes |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-403716SDCSS.pdf>
See store item page for other formats.