

# SCE-41VR2412 Cut Sheet



Saginaw enclosure, vented, NEMA 3R, 41 x 24 x 12in (HxWxD), wall mount, carbon steel, white, powder coat finish, single-door, 1/4-turn padlocking wing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-41VR2412>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Saginaw                      |
| <b>Item</b>                         | Enclosure                    |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | Yes                          |
| <b>NEMA Rating</b>                  | 3R                           |
| <b>IP Rating</b>                    | IP32                         |
| <b>Nominal Enclosure Dimensions</b> | 41 x 24 x 12in (HxWxD)       |
| <b>Enclosure Height</b>             | 41.00in                      |
| <b>Enclosure Width</b>              | 24.00in                      |
| <b>Enclosure Depth</b>              | 13.07in                      |
| <b>Mounting</b>                     | Wall                         |
| <b>Integral Mounting Feet</b>       | No                           |
| <b>Integral Mounting Flange</b>     | No                           |
| <b>Dual Access</b>                  | No                           |

|                                    |                                 |
|------------------------------------|---------------------------------|
| <b>Knockouts</b>                   | No                              |
| <b>Bottom Gland Plate</b>          | No                              |
| <b>Material</b>                    | Carbon steel                    |
| <b>Color</b>                       | White                           |
| <b>Finish</b>                      | Powder coat                     |
| <b>Cover Type</b>                  | Single-door                     |
| <b>Hinge Type</b>                  | Concealed hinges                |
| <b>Number of Hinges Per Door</b>   | 2                               |
| <b>Latch Type</b>                  | 1/4-turn padlocking wing handle |
| <b>Number Of Latches</b>           | 1                               |
| <b>Secondary Latch Type</b>        | 1/4-turn semi-flush             |
| <b>Number Of Secondary Latches</b> | 2                               |
| <b>Padlockable</b>                 | Yes                             |
| <b>Keylocking</b>                  | No                              |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |