

SCE-42XEL3716LPLG Cut Sheet



Saginaw Enviroline series disconnect enclosure, NEMA 3R/4/12/13, right flange, 42 x 37 x 16in (HxWxD), wall mount, carbon steel, RAL 7035 light gray, powder coat finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-42XEL3716LPLG>

Technical Specifications

| | |
|-------------------------------------|------------------------|
| Brand | Saginaw |
| Item | Disconnect enclosure |
| Series | Enviroline |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 3R/4/12/13 |
| IP Rating | IP66 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 42 x 37 x 16in (HxWxD) |
| Enclosure Height | 42.00in |
| Enclosure Width | 37.38in |
| Enclosure Depth | 17.10in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Knockouts | No |

| | |
|----------------------------------|---|
| Material | Carbon steel |
| Color | RAL 7035 light gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 3 |
| Latch Type | 3-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | Purchase subpanel separately |
| For Use With | Most major brand disconnect switches and circuit breakers |
| Additional Information | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |