

SCE-464919DCCSS6 Cut Sheet



Saginaw desk console, NEMA 3R/12/13, 46 x 49 x 19in (HxWxD), freestanding, dual access, 316L stainless steel, #4 brush finish, 2-door, 3-point keylocking flush swing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-464919DCCSS6>

Technical Specifications

Brand	Saginaw
Item	Desk console
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/12/13
IP Rating	IP55
Nominal Enclosure Dimensions	46 x 49 x 19in (HxWxD)
Enclosure Height	47.18in
Enclosure Width	49.25in
Enclosure Depth	25.57in
Mounting	Freestanding
Dual Access	Yes
Knockouts	No

Material	316L stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Number of Lid Hinges	3
Latch Type	3-point keylocking flush swing handle
Number of Door Latches	2
Secondary Latch Type	1/4-turn semi-flush latch
Number Of Secondary Latches	3
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement