

SCE-464919DCSS Cut Sheet



Saginaw desk console, NEMA 3R/4/4X/12/13, 46 x 49 x 19in (HxWxD), freestanding, dual access, 304 stainless steel, #4 brush finish, double-door, 3-point keylocking flush swing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-464919DCSS>

Technical Specifications

Brand	Saginaw
Item	Desk console
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	46 x 49 x 19in (HxWxD)
Enclosure Height	47.18in
Enclosure Width	49.25in
Enclosure Depth	25.57in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	Yes

Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Double-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Number of Lid Hinges	2
Latch Type	3-point keylocking flush swing handle
Number of Door Latches	4
Secondary Latch Type	1/4-turn semi-flush latch
Number Of Secondary Latches	3
Shelf	No
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-464919DCSS.pdf>
See store item page for other formats.