

# SCE-466019DCCSS Cut Sheet



Saginaw desk console, NEMA 3R/12/13, 46 x 60 x 19in (HxWxD), freestanding, dual access, 304 stainless steel, #4 brush finish, 2-door, 3-point keylocking flush swing handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-466019DCCSS>

## Technical Specifications

<b>Brand</b>	Saginaw	<b>Material</b>	304 stainless steel
<b>Item</b>	Desk console	<b>Finish</b>	#4 brush
<b>Subpanel</b>	Purchase subpanel separately	<b>Cover Type</b>	2-door
<b>Slope Top</b>	No	<b>Hinge Type</b>	Concealed hinges
<b>NEMA Rating</b>	3R/12/13	<b>Number of Hinges Per Door</b>	2
<b>IP Rating</b>	IP55	<b>Number of Lid Hinges</b>	3
<b>Nominal Enclosure Dimensions</b>	46 x 60 x 19in (HxWxD)	<b>Latch Type</b>	3-point keylocking flush swing handle
<b>Enclosure Height</b>	47.18in	<b>Number of Door Latches</b>	2
<b>Enclosure Width</b>	59.88in	<b>Secondary Latch Type</b>	1/4-turn semi-flush latch
<b>Enclosure Depth</b>	25.57in	<b>Number Of Secondary Latches</b>	3
<b>Mounting</b>	Freestanding	<b>Padlockable</b>	No
<b>Dual Access</b>	Yes	<b>Keylocking</b>	Yes
<b>Knockouts</b>	No		

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>