

SCE-48EL4812SSWFLP Cut Sheet



Saginaw Enviroline series enclosure, NEMA 3R/4/4X/12/13, 48 x 48 x 12in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-48EL4812SSWFLP>

Technical Specifications

Brand	Saginaw	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	No
Series	Enviroline	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	#4 brush
NEMA Rating	3R/4/4X/12/13	Cover Type	2-door
IP Rating	IP66	Hinge Type	Concealed hinges
Nominal Enclosure Dimensions	48 x 48 x 12in (HxWxD)	Number of Hinges Per Door	3
Enclosure Height	48.00in	Latch Type	3-point keylocking/padlocking combo handle
Enclosure Width	48.00in	Number Of Latches	2
Enclosure Depth	13.10in	Padlockable	Yes
Mounting	Wall	Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement