

SCE-48X2D7812 Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/12/13, right flange, 48 x 78 x 12in (HxWxD), freestanding/wall-mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-48X2D7812>

Technical Specifications

| | |
|-------------------------------------|-------------------------|
| Brand | Saginaw |
| Item | Disconnect enclosure |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 3R/12/13 |
| IP Rating | IP55 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 48 x 78 x 12in (HxWxD) |
| Enclosure Height | 48.00in |
| Enclosure Width | 77.75in |
| Enclosure Depth | 13.05in |
| Mounting | Freestanding/wall-mount |

| | |
|----------------------------------|------------------------------|
| Integral Mounting Feet | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | 2-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 3 |
| Latch Type | 3-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | Purchase subpanel separately |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-48X2D7812.pdf>
See store item page for other formats.