

SCE-48X4D15818 Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/12/13, right flange, 48 x 158 x 18in (HxWxD), freestanding/wall-mount, carbon steel, ANSI 61 gray, powder coat finish, 4-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-48X4D15818>

Technical Specifications

| | |
|------------------------------|-------------------------|
| Brand | Saginaw |
| Item | Disconnect enclosure |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 3R/12/13 |
| IP Rating | IP55 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 48 x 158 x 18in (HxWxD) |
| Enclosure Height | 48.00in |
| Enclosure Width | 157.50in |
| Enclosure Depth | 19.05in |
| Mounting | Freestanding/wall-mount |

| | |
|---------------------------|------------------------------|
| Integral Mounting Feet | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | 4-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 3 |
| Latch Type | 3-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | Purchase subpanel separately |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-48X4D15818.pdf>
See store item page for other formats.