

# SCE-48XEL3716SSST Cut Sheet



Saginaw Enviroline series disconnect enclosure, slope top, NEMA 3R/4/4X/12/13, right flange, 48 x 37 x 16in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-48XEL3716SSST>

## Technical Specifications

|                                     |                        |
|-------------------------------------|------------------------|
| <b>Brand</b>                        | Saginaw                |
| <b>Item</b>                         | Disconnect enclosure   |
| <b>Series</b>                       | Enviroline             |
| <b>Slope Top</b>                    | Yes                    |
| <b>Vented</b>                       | No                     |
| <b>NEMA Rating</b>                  | 3R/4/4X/12/13          |
| <b>IP Rating</b>                    | IP66                   |
| <b>Disconnect Mounting</b>          | Right flange           |
| <b>Nominal Enclosure Dimensions</b> | 48 x 37 x 16in (HxWxD) |
| <b>Enclosure Height</b>             | 52.26in                |
| <b>Enclosure Width</b>              | 37.38in                |
| <b>Enclosure Depth</b>              | 17.10in                |
| <b>Mounting</b>                     | Wall                   |
| <b>Integral Mounting Feet</b>       | No                     |
| <b>Integral Mounting Flange</b>     | No                     |

|                                  |   |
|----------------------------------|---|
| <b>Knockouts</b>                 | No  |
| <b>Material</b>                  | 304 stainless steel   |
| <b>Finish</b>                    | #4 brush  |
| <b>Cover Type</b>                | Single-door   |
| <b>Hinge Type</b>                | Concealed hinges  |
| <b>Number of Hinges Per Door</b> | 3   |
| <b>Latch Type</b>                | 3-point padlocking handle   |
| <b>Padlockable</b>               | Yes   |
| <b>Keylocking</b>                | No  |
| <b>Subpanel</b>                  | Purchase subpanel separately  |
| <b>For Use With</b>              | Most major brand disconnect switches and circuit breakers   |
| <b>Additional Information</b>    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |