

SCE-53XVR3716 Cut Sheet



Saginaw disconnect enclosure, vented, NEMA 3R, right flange, 53 x 37 x 16in (HxWxD), wall mount, carbon steel, white, powder coat finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-53XVR3716>

Technical Specifications

Brand	Saginaw
Item	Disconnect enclosure
Slope Top	No
Vented	Yes
NEMA Rating	3R
IP Rating	IP32
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	53 x 37 x 16in (HxWxD)
Enclosure Height	53.00in
Enclosure Width	37.38in
Enclosure Depth	17.07in
Mounting	Wall

Integral Mounting Feet	No
Material	Carbon steel
Color	White
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	3
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-53XVR3716.pdf>
See store item page for other formats.