

SCE-60EL6012LPPL Cut Sheet



Saginaw Enviroline series enclosure, NEMA 3R/4/12/13, 60 x 60 x 12in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-60EL6012LPPL>

Technical Specifications

Brand	Saginaw
Item	Enclosure
Series	Enviroline
Subpanel	Purchase subpanel separately
Slope Top	No
Vented	No
NEMA Rating	3R/4/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	60 x 60 x 12in (HxWxD)
Enclosure Height	60.00in
Enclosure Width	60.00in
Enclosure Depth	13.05in
Mounting	Floor

Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	3
Latch Type	3-point keylocking/padlocking combo handle
Number Of Latches	2
Padlockable	Yes
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement