

# SCE-60K4818SSST Cut Sheet



Saginaw sanitary enclosure, slope top, NEMA 3R/4/4X/12/13, 60 x 48 x 18in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 2-door, 1/4-turn sanitary stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-60K4818SSST>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Sanitary enclosure
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	Yes
<b>NEMA Rating</b>	3R/4/4X/12/13
<b>IP Rating</b>	IP69K
<b>Nominal Enclosure Height</b>	60in
<b>Nominal Enclosure Width</b>	48in
<b>Nominal Enclosure Depth</b>	18in
<b>Mounting</b>	Freestanding
<b>Dual Access</b>	No
<b>Knockouts</b>	No

<b>Material</b>	304 stainless steel
<b>Finish</b>	#4 brush
<b>Cover Type</b>	2-door
<b>Hinge Type</b>	Internal mount swing-out hinges
<b>Number of Hinges Per Door</b>	4
<b>Latch Type</b>	1/4-turn sanitary stainless steel latch
<b>Number Of Latches</b>	3
<b>Shelf</b>	No
<b>Padlockable</b>	No
<b>Keylocking</b>	No
<b>Includes</b>	SCE-PP1212 print pocket

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-60K4818SSST.pdf>  
See store item page for other formats.