

SCE-60K6012SSST Cut Sheet



Saginaw sanitary enclosure, slope top, NEMA 3R/4/4X/12/13, 60 x 60 x 12in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 2-door, 1/4-turn sanitary stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-60K6012SSST>

Technical Specifications

Brand	Saginaw
Item	Sanitary enclosure
Subpanel	Purchase subpanel separately
Slope Top	Yes
NEMA Rating	3R/4/4X/12/13
IP Rating	IP69K
Nominal Enclosure Height	60in
Nominal Enclosure Width	60in
Nominal Enclosure Depth	12in
Mounting	Freestanding
Dual Access	No
Knockouts	No

Material	304 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Internal mount swing-out hinges
Number of Hinges Per Door	4
Latch Type	1/4-turn sanitary stainless steel latch
Number Of Latches	3
Shelf	No
Padlockable	No
Keylocking	No
Includes	SCE-PP1212 print pocket

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-60K6012SSST.pdf>
See store item page for other formats.