

SCE-642432SSWS Cut Sheet



Saginaw workstation, NEMA 12/13, 64 x 24 x 32in (HxWxD), freestanding, dual access, 304 stainless steel, #4 brush finish, 2-door, 3-point keylocking flush swing handle, polycarbonate window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-642432SSWS>

Technical Specifications

Brand	Saginaw	Knockouts	No
Item	Workstation	Material	304 stainless steel
Subpanel	Purchase subpanel separately	Finish	#4 brush
Slope Top	No	Cover Type	2-door
NEMA Rating	12/13	Hinge Type	Concealed hinges
IP Rating	IP55	Latch Type	3-point keylocking flush swing handle
Nominal Enclosure Dimensions	64 x 24 x 32in (HxWxD)	Number of Door Latches	2
Enclosure Height	64.00in	Secondary Latch Type	1/4-turn semi-flush latch
Enclosure Width	24.25in	Number Of Secondary Latches	2
Enclosure Depth	34.39in	Window Material	Polycarbonate
Mounting	Freestanding	Padlockable	No
Dual Access	Yes	Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement